

# **Buckling Pin Relief Technology**










# **Buckling Pin**

### **Pressure Relief Devices**

BS&B produces fast acting/full opening buckling pin activated pressure relief devices (inline and angle discharge) designed to protect personnel, equipment and the environment from the dangers of overpressure. Buckling pin pressure relief devices combine the accuracy of rupture disks with the ability to be 'field-reset' while remaining installed after an overpressure event.



### **Features**

- Buckling pin pressure relief devices provide practical technology for the protection of applications containing one or more of the following conditions:
- Continuous processing (fast reset in the line)
- Hazardous service (limits operator exposure)
- Large line size (convenient reset in the line)
- High flow capacity
- Inaccessible location (external reset in the line)
- High operating pressure to set pressure ratio
- Sizes from 1 inch (25 mm) to 60 inches (1,500 mm)
- Cryogenic designs available
- ASME "UD" stamped, section XIII, division 1
- European Pressure Equipment Directive "CE" marked
- Back pressure independent options available (BPIV™)

### **Operating Pressure Ratio**

Buckling pin technology provides outstanding resistance to operating pressure conditions. The BPRV can be operated up to 95% of minimum set pressure. Subject to special testing, there is the ability to increase this ratio further.

### **Pressure Cycling Service**

Buckling pin devices are well suited to cyclic service pressure conditions. Operating under compression, the buckling pin is not subject to tensile fatigue failure. The BPRV can be subjected to pressure cycles up to its maximum operating pressure ratio with negligible impact to service life.

US patent numbers 6,367,498; 6,488,044 and 6,491,055 apply; International patents apply and pending

The BPAV™, BPRV™ and piping diagram icons are BS&B trademarks





## **BPRV**<sup>TM</sup>

### **Buckling Pin Relief Valve**

The BPRV offers the highest flow capacity and with convenient inline installation. After activation, the valve is manually reclosed and the pin replaced while the valve remains bolted between pipe flanges. This dramatically reduces plant downtime and personnel exposure. The pin is accessible in a lockable enclosure containing the BPRV mechanism. Valve installed sizes range from 2 inches (50mm) to 60 inches (1,500 mm).



On the downstream side of the disk, there are two shaft connections that hold the disk freely within the body. These are also fitted with standard fluoropolymer seals. Free rotation of the disk about the shaft is assured by the use of either bushings or bearings (depending upon size and set pressure) installed with a fluoropolymer seal on either side. The shaft seals are not in process contact from the inlet side when the BPRV is in the closed position. (Alternate shaft seals are available upon request).

As process pressure is applied to the disk, the rotational movement created by the connection of the disk to an offset shaft is translated into a mechanical force on the pin, via the valve mechanism, which is installed in the mechanism outside of the piping.

### **Size and Set Pressure Capability**

The BPRV is available with a standard range of sizes and set pressures designed to suit applications that are compatible with ANSI 150, DIN PN 10 or similar flange specifications. In addition to these standard specifications, the BPRV is capable of meeting a wide range of dedicated customer requirements which have already included:

- High set pressures: Over 2,000 psi (138 bar) in a 6 inch (150 mm) nominal size installed between ANSI 900 flanges
- Low set pressure: 1.5 psig (100 mbar) in a 24 inch (600 mm) nominal size

# Set Pressure Certification and Tolerance

In line with international standards, the BPRV is certified at the customer requested set pressure. This certification is a result of buckling pin tests conducted in the BPRV to confirm compliance with set pressure and tolerance expectations. The BPRV is certified with a single set pressure tolerance, as indicated in the table below. For set pressures above 20 psi (1.4bar), the BPRV provides a superior set pressure tolerance of +/-5% compared to other non-reclosing pressure relief devices.

When certified according to ASME / North American standards, the BPRV is marked with the customer requested set pressure. When certified according to European (PED) standards, the BPRV is marked with the customer requested set pressure and the tolerance based upon the table below. Alternatively, European certification allows for marking the BPRV with a minimum / maximum set pressure (which will also be calculated from the table).

Pressure	Tolerance
From 1-40 psi (0.07-2.76 bar)	<u>+</u> 2 psi standard (0.14 bar)
Over 20 psi (1.4 bar)	±5% standard

Alternative tolerances available upon request. Please consult BS&B with your special applications



### **3 Set Pressure Calibration Controls**

- The offset of the BPRV disk shaft from the center line:
   A large offset will generate a higher shaft load; a small offset will generate a lower shaft load. The BPRV is designed with the optimal offset based on set pressure requirements.
- The buckling strength of the buckling pin: This is a
  function of the 4th power of the pin diameter, the modulus of
  elasticity of the pin material, and the inverse of the pin length.
  Buckling pin diameter is used for significant set pressure
  tuning, length adjustment is used for fine tuning.
- The mechanism lever: This enables a wide range of BPRV set pressures to be obtained with modest buckling pin lengths and diameters while using an established disk shaft offset. This allows the mechanism to be compact and results in a simple pin installation and procedure that can be completed by a single operator in minutes without special tools.

**Note:** The BPRV is calibrated before shipment to meet the users required set pressure and tolerance.


### **Materials of Construction**

The user may specify the material of construction for each of the three major BPRV components, standard materials are as follows:

- Valve body: The standard materials are carbon steel and stainless steel. Alternate materials include duplex, Hastelloy® C-276, Monel®, Inconel® 625, Titanium metals that can be obtained in the form of cut plate or a forging (depending upon the size of the device to be fabricated)
- Valve disk: The standard material is stainless steel. The disk provides the valve sealing surface, therefore a resistant surface must be ensured. Alternate materials are the same as for the valve body
- Enclosure: The standard material is stainless steel with Viton® door seals. Alternates may be requested

### **Seals**

The primary seal in the BPRV is mounted in the 1-piece body, held in place by a sealing ring. This seal engages a curved surface on the leading edge of the disk and has a profile that provides a tight shut-off from both the inlet and outlet sides of the device. The standard seal material is fluoropolymer (alternates are available upon request).



**BPRV Valve in Closed Position** 

### **3 Primary BPRV Components**

**Rotating disk:** A rotating disk normally closes the flow path and turns through 90 degrees in response to an overpressure/ underpressure condition. The rotating disk is constructed from metal and has a hollow design. This maximizes the flow path through the BPRV and ensures the stability of the disk during normal service and at the time of opening.

**Flanged body:** A flanged body contains the rotating disk, holding it in place using shaft connections that are sealed within the body and pass through bearings to permit free rotation of the disk within the body. The body is a 1-piece design with no constructional welds or other potential external leak paths.

**External enclosure and mechanism:** The external enclosure and mechanism provides the set pressure control for the BPRV. The mechanism is designed to resist the turning moment of the disk shaft during normal service pressure conditions. When the desired set pressure is reached, the mechanism releases the disk due to the function of a buckling pin which has been built with sufficient strength to resist disk rotation until that point. The mechanism is contained within a stainless steel enclosure. The enclosure door includes a seal to permit service under severe environmental conditions.



### **Temperature**

The materials of construction for the BPRV permit a wide range of extreme service temperatures ranging from cryogenic to high-heat temperatures. Please review your temperature needs with BS&B. Each device has two different temperature considerations:

- Compatibility of service temperature with seal materials
- Buckling pin coincident temperature at time of function

### **Enclosure and Mechanism Construction**

Three standard mechanisms are employed to meet the torque requirements of the BPRV nominal sizes 2-60 inches (50-1,500 mm):

- M600 mechanism: low torque applications typical for sizes 2-6 inches (50-150 mm)
- M4200 mechanism: Torque ranges typical for higher pressure 4 inch (100 mm) BPRV devices through low pressure 24 inch (600mm) size
- M16000 mechanism: for high torque requirements of BPRV devices sized 20-60 inches nominal size

The mechanism front cover is provided with a latch tongue that aligns with another on the side to allow the user to add a preferred locking mechanism. Turn latches mounted on the front of the enclosure energize the door elastomer seal.

All mechanisms comprise of stainless steel and protective coated high tensile steel components. This combination avoids seizing of moving parts through the use of similar metals, and provides excellent corrosion resistance. The mechanism is fully sealed within the enclosure when the door is latched shut.

### **Customized BPRV Units/Command Activation**

The BPRV can be command activated in two different configurations:


If it is known that the BPRV will always sense a positive differential pressure, an actuator (e.g. solenoid or pneumatic piston) installed adjacent to the buckling pin can be used to buckle the pin on demand. This will release the BPRV mechanism and allow the disc to rotate freely under pressure.

This is known as a CAE (command activated enclosure) and allows the valve to be used as both a pressure relief device and a command actuated quick opening valve.

If command actuation is desired in an application where positive differential pressure cannot be guaranteed, a powered actuator can be installed on the free shaft of the BPRV. When the operating conditions require the valve open, the actuator is powered to overcome both the buckling pin and any back pressure induced torque on the BPRV shaft to open the device.

This is known as a CAS (command activated shaft) and allows the BPRV to be used as both a pressure relief device and a command actuated quick opening valve.

The BPRV-CAE and BPRV-CAS are examples of customized design options that can be satisfied with this versatile pressure relief technology. BS&B welcomes the opportunity to develop solutions to unique applications.



**Mechanism Function** 

fulcrum to the lever load output), the BPRV will open. The input load is provided by the pressure generated torque on the disc shaft This loads the input side of the lever arm. When the buckling pin operates, the lever is free to move, allowing the shaft to rotate through 90 degrees into the full open position. At most set pressures, the BPRV will latch in the full open position to ensure the greatest flow rate through the device. The location

of the fulcrum is tailored by BS&B during the calibration of each BPRV. This set pressure control feature of the BPRV design is used for fine tuning. The fulcrum location is factory set and wire sealed for tamper evidence.



### Installation

The BPRV is designed for "in-line" installation between pipe flanges. Each device is a 'full face' design with the pipe flange bolting typically passing through the perimeter of the body. Some flange specifications have a compact bolting pattern that would interfere with the bushings or bearings if through bolt holes were used; in these cases, a threaded blind bolt hole is provided on both sides of the BPRV so a full set of flange bolts is installed. The piping may run horizontally, vertically, or at an oblique angle. The BPRV can be supplied set-pressure certified for any of these orientations. The user must identify the installation configuration at time of order to ensure appropriate calibration testing of the BPRV. The BPRV body can be fitted with lifting lugs to ease maneuver of the device into place between pipe flanges.

### Field Reset

When a buckling pin has functioned and the BPRV is to be reset, this can typically be accomplished while the device remains installed in the piping system. The enclosure is opened, the used buckling pin removed, the disk rotated back into the closed position, a replacement buckling pin installed and the mechanism reset. This takes only a few minutes and can be completed by a single operator, even with the largest size BPRV.

### **Maintenance**

As desired, the buckling pin can be removed and the BPRV tested by rotating the disk into the open position triggering the mechanism. There must be no pressure on the device. The buckling pin can then be re-installed.

Occasionally it will be necessary to replace the main body seal. This can be accomplished quickly and easily. The main body seal is held in place by a seal retainer ring that inserts into the inlet of the one-piece body. This seal ring is simply removed, using simple tools, and the used seal pulled out from the BPRV body. After inspecting the seating area and clearing away any debris, the BS&B replacement seal is installed and the seal ring put back in place. Seal replacement does not require disassembly of the BPRV body or mechanism. It is recommended a spare main body seal is purchased for each BPRV.

### **Testing In Place**

Since the BPRV might be interpreted as a relief valve, many users wish to perform scheduled maintenance to ensure the set pressure has not been compromised while the valve is in service. The normal procedure for testing of many types of relief valves is to remove the valve from service and send to a valve repair shop for a pop test and re-certification. The advantage of the BPRV is that the valve can be re-tested in-situ. The offset shaft is designed with a hexagon drive in the enclosure. The user can leave the valve in service between the flanges and attach a torque wrench to the hex. All the user needs to do is remove the pin and load the shaft with a torque wrench until the valve opens. BS&B can supply a torque value range which, when applied to the hex drive of the offset shaft. Once the value recorded on the torque wrench lies within this torque range supplied by BS&B, the user knows that the valve set pressure has not been compromised and the product is now re-tested. This allows users to re-check the valve within 10 to 15 minutes, without having to remove it from the pipeline.

Testing in place greatly reduces the maintenance expenses compared with relief valves by dramatically reducing the time and labor involved with the re-validation process. BS&B recommends these activities are supervised by a BS&B trained and authorized technician.



**API 537 Compliant Application** 





US patent 6,484,742 and international patents apply

### Optional Saf-T-Pin™ Buckling Pin Cartridge

The BPRV can be provided with buckling pin cartridges that are installed like an electrical fuse. The Saf-T-Pin buckling pin cartridge allows a "quick-change" option of

buckling pins with a simple push-in/pull-out design for installation within the enclosure. Each Saf-T-Pin cartridge contains a calibrated buckling pin that is perfectly mounted for optimum performance.

The Saf-T-Pin cartridge locks into the BPRV mechanism in one direction only, ensuring fail-safe installation. The transparent cartridge permits visual inspection of the buckling pin, and the stainless steel ends of the cartridge are marked with full set pressure and traceability information including the serial number of the BPRV device. The Saf-T-Pin cartridge avoids the need for special installation procedures and any concern of handling bare buckling pins.

### **Sensor/Indicator Option**

Both a visual and electrical signal to confirm BPRV status is available. Mounted on the free shaft not used by the mechanism, the standard BPRV sensor comprises a sealed enclosure (typically to Nema IV standard) that houses a colored dome indicating 'open' (colored red) or 'closed' (colored green). The dome is rotated by a shaft extension that moves in unison with the disk of the BPRV. Electrical switching compatible with the users requirements can be added to the enclosure to provide a remote signal or alarm when the BPRV operates. This can be provided to meet intrinsically safe requirements.

### SmartDisk™ Compatible

The BPRV can be supplied with SmartDisk wireless sensor technology that allows an electrical signal to be generated at a monitoring station located up to several thousand feet away from the BPRV without the cost of hard wiring.

### **Quality Assurance**

Every BPRV is thoroughly tested before shipment. Pre-delivery inspection can be divided into:

- Dimensional inspection
- · Leak tightness verification
- Buckling pin calibration and set pressure testing

Before the BPRV is assembled from component parts, each component is dimensionally verified for its critical features. After assembly the performance of the seals is checked, the Fluid Controls Institute specification is typically followed with a minimum test standard of class IV established. Many BPRV devices are supplied to the stricter class V and class VI limits which require a 'bubble tight' construction. The BPRV is third party certified by ASME and PED. Thus all standard valves can be ASME "UD" stamped and/or "CE" marked.

All buckling pins that are supplied as a lot are manufactured from a single batch of raw material at the same time. The BPRV set pressure is established through buckling pin destructive testing. Once the appropriate pin configuration has been achieved for the required set pressure, the lot of pins is completed within very tight dimensional tolerances. BS&B quality assurance personnel witness set pressure tests for certification purposes. All buckling pins are supplied tagged with a traceable lot number, set pressure and the serial number of the BPRV unit for which they have been calibrated. Saf-T-Pin<sup>TM</sup> buckling pin cartridges are recommended for optimum control and traceability.


When fully calibrated and certified, wire seals are installed at the following key locations:

- · Junction of the body and the enclosure
- Fulcrum connection to the enclosure baseplate
- Junction of the sensor to the shaft (where fitted)

### **Codes and Standards**

Several international standards recognize buckling pin devices and provide guidelines for their certification. These include ASME Section XIII, UG-138, TUV AD Merkblatt A1 and the European Pressure Equipment Directive (PED). The BPRV can be "UD" and / or "CE" marked.





The BPIV is the same as the BPRV, but is back pressure independent.

# BPIV<sup>TM</sup> Buckling Pin Inlet Valve The BS&B BPIV set pressure is controlled by a precision buckling pin

The BS&B BPIV set pressure is controlled by a precision buckling pin which is calibrated to respond to the forces generated by inlet pressure acting on the valve disk independent of any back pressure that may be present. When the pin activates, the valve disk rotates to achieve a full diameter flow area. The BPIV has a soft seat. Standard valve materials are carbon steel and stainless steel for process contact components. Special materials are available upon request.



BPIV Buckling Pin Mechanism (Closed Position)

### **BPRV** and **BPIV** Capabilities

Inlet size	Flow area	Set Pressure	ASME		
		Range			
2 NPS	2.75 sq in	15 - 2250 psi	XIII div 1		
3 NPS	6 sq in	15 - 2250 psi	XIII div 1		
4 NPS	10 sq in	15 - 2250 psi	XIII div 1		
6 NPS	23.5 sq in	1 - 2250 psi	XIII div 1		
8 NPS	39.65 sq in	1 - 2250 psi	XIII div 1		
10 NPS	62.48 sq in	1 - 2250 psi	XIII div 1		
12 NPS	90.5 sq in	1 - 2250 psi	XIII div 1		
14 NPS	109 sq in	1 - 2250 psi	XIII div 1		
16 NPS	149 sq in	1 - 1440 psi	XIII div 1		
18 NPS	196.2 sq in	1 - 1440 psi	XIII div 1		
20 NPS	239.1 sq in	1 - 1440 psi	XIII div 1		
24 NPS	367.6 sq in	1 - 720 psi	XIII div 1		
30 NPS	601 sq in	1 - 720 psi	XIII div 1		
32 NPS	614 sq in	1 - 720 psi	XIII div 1		
34 NPS	695 sq in	1 - 720 psi	XIII div 1		
36 NPS	781 sq in	1 - 720 psi	XIII div 1		
38 NPS	872 sq in	1 - 720 psi	XIII div 1		
40 NPS	968 sq in	1 - 720 psi	XIII div 1		
42 NPS	1069 sq in	1 - 720 psi	XIII div 1		
44 NPS	1175 sq in	1 - 720 psi	XIII div 1		
46 NPS	1286 sq in	1 - 720 psi	XIII div 1		
48 NPS	1403 sq in	1 - 720 psi	XIII div 1		
52 NPS	1650 sq in	1 - 720 psi	XIII div 1		
54 NPS	1784 sq in	1 - 720 psi	XIII div 1		
56 NPS	1918 sq in	1 - 720 psi	XIII div 1		
60 NPS	2206 sq in	1 - 720 psi	XIII div 1		



## **BPAV**<sup>TM</sup>

### **Buckling Pin API-Series Valve**

The BS&B BPAV set pressure is controlled by a precision buckling pin that is calibrated to respond to the forces generated by inlet pressure acting on the valve plug. When the pin activates, the valve plug lifts to achieve a full diameter flow area. The BPAV has a soft seat. Standard valve materials are carbon steel and stainless steel for process contact components. Special materials are available upon request.

- The first API-526 piping configuration buckling pin valve
- 1 x 1.5 inches (25 x 40 mm) to 8 x 10 inches (200 x 250 mm size range); Larger sizes available upon request
- Full bore relief for maximum flow capacity; 0.8 coefficient of discharge / Kd = 0.8 for gas, Kd = 0.686 for liquid
- Fast acting
- Set pressure independent of back pressure, suitable for variable back pressure applications
- Operable to 90% of set pressure no simmering
- · Suitable for gas, liquid and two-phase flow
- Higher flow capacity than equivalent sized relief valve
- ANSI / ASME EN / DIN JIS flange compatibility, GOST
- ASME "UD" stamped, Section VII, Division I
- Pressure Equipment Directive "CE" marked

Hastelloy® is a trademark of Haynes International Inc. Monel® and Inconel® are trademarks of Corporation. Viton®is a registered trademark of The Chemours Company.

### **Benefits**

- Direct replacement of API series relief valves no piping modifications
- Capacity of the BPAV exceeds the largest API size orifice per line size - Kd = 0.8 - ideal solution for brown-field projects; 0.686 for liquid
- More flow per line size than a relief valve
- Increased production capacity for same piping configuration
- Smaller size BPAV may be adequate for application
- Reducing valve cost, piping cost and weight critical for offshore applications

### **Available with Replaceable Seat**

The BPAV is available with a replaceable seat, which is applied to corrosive and errosive environments that would result in frequent seat replacements. The replaceable seat can also be applied to high H2S processes where the replaceable seat material needs to be of a higher alloy (eq. Inconel 625).

### **BPAV-LPTM**

Low set pressure buckling pin API series valve for set pressures below 25 psig (1.72bar).

### Sizes

- 2 x 3 inches (50 x 80mm)
- 3 x 4 inches (80 x 100mm)
- 4 x 6 inches (100 x 150mm)
- 6 x 8 inches (150 x 200mm)
- 8 x 10 inches (200 x 250mm)

### **BPAV™** Air Capabilities

Inlet Size	Outlet Size	Flow Area*	Orifice (Designator) Diameter	Set Pressure Range	Media	ASME
1 NPS	1.5 NPS	0.72 in	0.957 in	2100 -3500 psi	Air	XIII Div 1
I INPS	1.5 NP5	0.86 in	1.046 in	15-2100 psi	Air	XIII Div 1
1.5 NPS	2 NPS	2.04 in	1.612 in	15-1440 psi	Air	XIII Div 1
2 NPS	3 NPS	3.36 in	2.067 in	15-720 psi	Air	XIII Div 1
3 NPS	4 NPS	7.39 in	3.067 in	15-720 psi	Air	XIII Div 1
4 NPS	6 NPS	12.73 in	4.026 in	15-720 psi	Air	XIII Div 1
6 NPS	8 NPS	28.89 in	6.065 in	15-275 psi	Air	XIII Div 1
8 NPS	10 NPS	50.03 in	7.981 in	15-275 psi	Air	XIII Div 1

<sup>\*</sup>Minimum Net Flow Area (MNFA)



### **BPAV™ Liquid Capabilities**

Inlet Size	Outlet Size	Flow Area*	Orifice (Designator) Diameter	Set Pressure Range	Media	ASME
1 NPS	1.5 NPS	0.72 in	0.957 in	2100 -3500 psi	Water	XIII Div 1
LINES	1.5 NP3	0.86 in	1.046 in	50-2100 psi	Water	XIII Div 1
1.5 NPS	2 NPS	2.04 in	1.612 in	15-1440 psi	Water	XIII Div 1
2 NPS	3 NPS	3.36 in	2.067 in	15-720 psi	Water	XIII Div 1
3 NPS	4 NPS	7.39 in	3.067 in	15-720 psi	Water	XIII Div 1
4 NPS	6 NPS	12.73 in	4.026 in	15-720 psi	Water	XIII Div 1
6 NPS	8 NPS	28.89 in	6.065 in	15-275 psi	Water	XIII Div 1
8 NPS	10 NPS	50.03 in	7.981 in	15-275 psi	Water	XIII Div 1

<sup>\*</sup>Minimum Net Flow Area (MNFA)

### **BPAV dimensions**


in	mm		A	ı	3		C	[	)	ı	E	ı	F	(	i	ŀ	1		ı
""		in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
1 x 1.5	25 x 40	26	660	0.9	24	1.0	27	4.9	124	1.1	29	1.5	38	6.1	155	4.1	105	4.5	114
1.5 x 2	40 x 50	31	787	1.1	29	1.6	41	6.1	155	1.3	32	1.9	49	6.5	165	4.9	124	6.0	152
2 x 3	50 x 80	31	787	0.9	22	2.1	53	6.5	165	1.1	29	2.9	74	8.3	211	5.4	136	4.9	124
3 x 4	80 x 100	36	914	1.1	29	3.1	78	8.3	211	1.3	32	3.8	97	10.0	254	6.1	156	6.4	162
4 x 6	100 x 150	36	914	1.3	32	4.0	102	10.0	254	1.4	37	5.8	146	12.5	318	7.8	197	8.3	210
6 x 8	150 x 200	46	1168	1.4	37	6.1	154	12.5	318	1.6	41	7.6	194	15.0	381	9.4	240	9.5	241
8 x 10	200 x 250	56	1422	1.6	41	8.0	203	15.0	381	1.9	47	9.6	243	17.5	445	10.9	276	11	279

BPAV air/gas

in	mm	Minimum S	et Pressure	Maximum Set Pressure		
		psig	barg	psig	barg	
1 x 1.5	25 x 40	15	1.03	3500	241.31	
1.5 x 2	40 x 50	15	1.03	1440	99.31	
2 x 3	50 x 80	15	1.03	720	49.66	
3 x 4	80 x 100	15	1.03	720	49.66	
4 x 6	100 x 150	15	1.03	720	49.66	
6 x 8	150 x 200	15	1.03	275	18.97	
8 x 10	200 x 250	15	1.03	275	18.97	

### **BPAV liquid**

DIA IIdaia										
mm	Minimum S	et Pressure	Maximum Set Pressure							
	psig	barg	psig	barg						
25 x 40	50	3.45	3500	241.31						
40 x 50	15	1.03	1440	99.31						
50 x 80	15	1.03	720	49.66						
80 x 100	15	1.03	720	49.66						
100 x 150	15	1.03	720	49.66						
150 x 200	15	1.03	275	18.97						
200 x 250	15	1.03	275	18.97						
	mm  25 x 40  40 x 50  50 x 80  80 x 100  100 x 150  150 x 200	mm         Minimum S           psig         25 x 40         50           40 x 50         15           50 x 80         15           80 x 100         15           100 x 150         15           150 x 200         15	mm         Minimum Set Pressure           psig         barg           25 x 40         50         3.45           40 x 50         15         1.03           50 x 80         15         1.03           80 x 100         15         1.03           100 x 150         15         1.03           150 x 200         15         1.03	mm         Minimum Set Pressure         Maximum Set Pressure           psig         barg         psig           25 x 40         50         3.45         3500           40 x 50         15         1.03         1440           50 x 80         15         1.03         720           80 x 100         15         1.03         720           100 x 150         15         1.03         720           150 x 200         15         1.03         275						



# **BPPV™** Buckling Pin Pilot Valve

The BPPV is a buckling pin pilot valve ranging from  $6 \times 6$  inches through  $30 \times 30$  inches (150 x 150mm through 1,220 x 1,220mm) with a set pressure from 10 to 275 psig (0.69 to 18.96 barg). Larger sizes to  $48 \times 48$  inches are also available.

Inlet size	Outlet size	Flow area	Orifice (designator) diameter	Lift	Set pressure range	Media	Code section
6 NPS	6 NPS	28.3 in <sup>2</sup>	6.0 in	3.0 in	15 - 275 psi	Air	XIII div 1
8 NPS	8 NPS	49.0 in <sup>2</sup>	7.9 in	4.0 in	15 - 275 psi	Air	XIII div 1
10 NPS	10 NPS	77.9 in <sup>2</sup>	9.9 in	5.0 in	15 - 275 psi	Air	XIII div 1
12 NPS	12 NPS	110.9 in <sup>2</sup>	11.9 in	6.0 in	15 - 275 psi	Air	XIII div 1
14 NPS	14 NPS	135.2 in <sup>2</sup>	13.1 in	6.6 in	15 - 275 psi	Air	XIII div 1
16 NPS	16 NPS	179.1 in <sup>2</sup>	15.1 in	7.6 in	15 - 275 psi	Air	XIII div 1
18 NPS	18 NPS	229.1 in <sup>2</sup>	17.1 in	8.5 in	15 - 275 psi	Air	XIII div 1
20 NPS	20 NPS	285.3 in <sup>2</sup>	19.1 in	9.5 in	15 - 275 psi	Air	XIII div 1
24 NPS	24 NPS	416.2 in <sup>2</sup>	23.0 in	11.5 in	15 - 275 psi	Air	XIII div 1
30 NPS	30 NPS	658.7 in <sup>2</sup>	29.0 in	14.5 in	15 - 275 psi	Air	XIII div 1



# **BPCV™** Buckling Pin Valve

### **Common Inlet and Outlet Connection Size**

The BS&B type BPCV's set pressure are controlled by a precision buckling pin which is calibrated to respond to the forces generated by inlet pressure acting on the valve plug. When the pin activates, the valve plug lifts to achieve a full diameter flow area. The valves have a soft seat.

#### Standard BPCV Sizes

- 1 x 1 inch (25 x 25mm)
- 1.5 x 1.5 inches (40 x 40mm)
- 2 x 2 inches (50 x 50mm)
- 3 x 3 inches (80 x 80mm)
- 4 x 4 inches (100 x 100mm)
- 6 x 6 inches (150 x 150mm)
- 8 x 8 inches (200 x 200mm)

For individual valve dimensions, contact BS&B. Alternative sizes available upon request.

#### **Features**

Angle valve design for connection to vertical inlet piping/ horizontal outlet piping

- Inlet and outlet flange connections for ANSI/ASME EN/ DIN - JIS flange compatibility
- Same nominal size inlet and outlet connections, suitable for bypass applications
- Higher flow capacity than equivalent inlet size relief valve
- Operable to 90% of minimum set pressure
- Set pressure independent of back pressure provided inlet pressure exceeds back pressure

Standard valve materials are carbon steel and stainless steel for process contact components. Special materials are available upon request.

### **BPCV Pressure Capabilities**

Inlet Size	Outlet Size	Flow Area*	Orifice (Designator) Diameter	Set Pressure Range	Media
1 NPS	1 NPS	0.72 in <sup>2</sup>	0.957 in	2100 -3500 psi	Gas / Liquid
TINES	TINES	0.86 in <sup>2</sup>	1.046 in	50-2100 psi	Gas / Liquid
1.5 NPS	1.5 NPS	2.04 in <sup>2</sup>	1.612 in	15-1440 psi	Gas / Liquid
2 NPS	2 NPS	3.36 in <sup>2</sup>	2.067 in	15-720 psi	Gas / Liquid
3 NPS	3 NPS	7.39 in <sup>2</sup>	3.067 in	15-720 psi	Gas / Liquid
4 NPS	4 NPS	12.73 in <sup>2</sup>	4.026 in	15-720 psi	Gas / Liquid
6 NPS	6 NPS	28.89 in <sup>2</sup>	6.065 in	15-275 psi	Gas / Liquid
8 NPS	8 NPS	50.03 in <sup>2</sup>	7.981 in	15-275 psi	Gas / Liquid
10 NPS	10 NPS	78.58 in <sup>2</sup>	10.020 in	15-275 psi	Gas / Liquid
12 NPS	12 NPS	113.10 in <sup>2</sup>	11.938 in	15-275 psi	Gas / Liquid
14 NPS	14 NPS	137.89 in²	13.124 in	15-275 psi	Gas / Liquid







### **AMERICAS**

#### Tulsa, OK USA

T: +1 918 622 5950 F: +1 918 665 3904 E: sales@bsbsystems.com

#### **Houston, TX USA**

T: +1 713 682 4515 F: +1 713 682 5992 E: sales@bsbsystems.com

#### Minneapolis, MN USA

T: +1 952 941 0146 F: +1 952 941 0646 E: sales@bsbipd.com

#### **Edmonton, AB Canada**

T: +1 780 955 2888 F: +1 780 955 3975 E: contacts@bsbprocess.com

#### **Monterrey, Mexico**

T: +011 52 81 8299 5861 T: +011 52 81 8299 5862 E: sales@bsbsystems.com

#### Sao Paulo, Brasil

T: +55 11 2084 4800 F: +55 11 2021 3801 E: sales@bsbbrasil.com

# EUROPE, MIDDLE EAST & AFRICA

#### Limerick. Ireland

T: +353 61 484700 F: +353 61 227987 E: sales@bsb.ie

#### Düsseldorf. Germany

T: +49 211 930550 F: +49 211 3982171 E: info@bormann-neupertbsb.de

#### Manchester. UK

T: +44 161 955 4202 F: +44 161 870 1086 E: sales@bsb-systems.co.uk

#### The Hague, The Netherlands

T: +31 70 362 2136 F: +31 70 360 4724 E: info@bsbsystems.nl

#### Copenhagen, Denmark

T: +45 3318 9000 F: +45 3318 9001 E: info@bsbsystems.dk

#### **United Arab Emirates**

T: +971 (0) 55 518 0314 T: +971 (0) 55 518 0916 F: +971 (0) 2 558 9961 E: sales@bsbsystems.ae

### **ASIA PACIFIC**

### Singapore

T: +65 6513 9780 F: +65 6484 3711 E: sales@bsb.com.sq

#### Yokohama, Japan

T: +81 45 450 1271 F: +81 45 451 3061 E: information@bsb-systems.co.jp

#### Seoul, South Korea

T: +82 2 2636 9110 F: +82 2 2636 9120 E: sales@bsbsystems.kr

#### Shanghai, China

T: +86 21 6391 2299 F: +86 21 6391 2117 E: sales@bsbsystems.com

#### Chennai, India

T: +91 44 2450 4200 F: +91 44 2450 1056 E: sales@bsbsystems.com







### Visit our website for the most complete, up-to-date information

Products, specifications and all data in this literature are subject to change without notice. Questions regarding product selection and specifications for specific applications should be directed to BS&B. All sales are subject to the BS&B companies' standard terms and conditions of sale. Nothing herein should be construed as a warranty of merchantability or fitness for a particular purpose.

### www.bsbsystems.com | www.bsb.ie

© 2019 BS&B Innovations, Limited. Updated November 2024.